


TECHNICAL DATA SHEET
NBVE series



NBVE 110/110 P RC
 DUAL PURPOSE UV-C FLOW GERMICIDAL LAMP

HOW DOES THE DUAL PURPOSE UV-C FLOW GERMICIDAL LAMP WORK?

Dual purpose UV-C flow germicidal lamps with external UV-C bulbs of direct action guarantee a full range of disinfection. It gives a possibility of intensive disinfection of the air in the presence of people (UV-C flow chamber – function I) and direct disinfection of the whole room when the staff and patients stay outside the room (UV-C direct radiation tube – function II). Functions can be turned on/off separately or both at once.

BASIC DATA:

Air flow disinfection function (flow disinfection chamber)	yes
Direct radiation function	yes
Presence of people, animals, plants inside the room during disinfection process	allowed / not allowed flow function / direct radiation function
Mounting type	on mobile stand
Mounting on five arm mobile stand	yes (provides stability)
Working time counter	no
RC remote control	yes, in standard
External bulbs	yes, 2 bulbs
Casing material*	INOX steel
Anti-dust filters	yes, 1 filter inside the device, 5 additional pcs. for each lamp
Switch on/off	2 separate switches to each function built in lamp body
Ambient temperature	+10°C to +40°C
Relative humidity	30% to 70%
Atmospheric pressure	700 hPa to 1060 hPa
Declaration of conformity	yes
User's manual English version	yes

*white color version of NBVE lamps on demand in the same price

TECHNICAL DATA SHEET

NBVE series

NBVE 110/110 P RC

DUAL PURPOSE UV-C FLOW GERMICIDAL LAMP

TECHNICAL DATA:

Supply voltage	230 V, 50 Hz
Power consumption	185 W
UV-C bulbs (Philips/Osram)	internal: 2 x 55 W (TUV/HNS) external: 2 x 55 W (TUV/HNS)
UV-C radiation wave - length	253.7 nm
Useful lifetime of the UV-C bulbs	min. 8000 h
Radiation intensity of the external UV-C tube at the distance of 1 m	150 µW/cm ²
Fan capacity	199 m ³ /h
Cubage of disinfected room	45-90 m ³
Effective area of the lamp	18-36 m ²
Class of protection against electric shock	I
Ingress Protection Code	IP 20
Lamp body dimensions (L x W x H)	355 x 130 x 1125 mm
Overall dimensions (L x W x H)	600 x 600 x 1300 mm
Total lamp mass	12.5 kg
Stand length	118 cm
Power cord length	3 m, ended with the socket plug

APPLICATION RECOMMENDATIONS:

Hospitals

- operation theatres
- intensive care units
- emergency rooms
- examination and treatment rooms
- reception units
- patient rooms, isolation rooms
- soiled/dirty utility rooms

- Outpatient clinics**
- Medical laboratories**
- Chemist's**
- Beauty salons**

HoReCa

- SPA
- hotels
- restaurants
- catering/café

RC remote control provided with lamp

